

**Value pack flow drill - flat (no collar) long Uni, 5 pieces****Order data**

Order number	GG0757 M3
GTIN	4069515043021
Item class	GGN

Description**Version:**

Very quickly produce core holes in thin-walled materials using frictional heat. Can be used on CNC, NC and pillar drilling machines.

Flow drill - flat (no collar), **same as No. 080757.**

Standard or long; with or without a collar.

Application:

Suitable for steel, stainless steel, aluminium, copper, brass.

Suitable for:

HOLEX ER collets No. 308964, ER chuck key No. 309680, HOLEX fluteless tap No. 139130 or No. 139180 and HOLEX holder M-Drill No. 080750.

Technical description

Material thickness	0.7 - 4 mm
recommended speed	3000 min ⁻¹
Tapping hole Ø	2.7 mm
Shank Ø	6 mm

recommended drive power	0.7 kW
Contents	5" pcs.
Type of product	Flow drills

Suitable products

No Shop URL available for: GG0757 M3