

**Value pack WNMG indexable insert roughing 30 pieces HB7035-2****Order data**

Order number	GG2494 080408
GTIN	4067263092278
Item class	GGN

Technical description

Contents	252208 HB7035-2
Main application	P
Cutting speed v_c main application	100 - 290 mm/min
Tool material	Carbide
Finishing/roughing assignment	Roughing
Number of changes/inserts	6
Cutting depth a_p	1.5 - 6 mm
Corner radius	0.8 mm
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.25 - 0.6 mm/rev.
ISO code indexable insert	WNMG 080408
Cutting depth $a_{p \max}$	2.75 mm
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2494 080408
