



DCMT indexable insert for finishing 30 pieces, HBT020, Size: 11T302



Order data

Order number	GG3936 11T302
GTIN	4067263092278
Item class	GGN

Technical description

Main application	P
Cutting depth $a_{p \max}$	2.75 mm
Contents	260377 HBT020
Cutting speed v_c main application	120 - 330 mm/min
Number of changes/inserts	2
Corner radius	0.2 mm
Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.1 - 0.3 mm/rev.
Coating	TiCN
ISO code indexable insert	DCMT 11T302
Tool material	Carbide

Data sheet

Finishing/roughing assignment	Finishing
Cutting depth a_p	0.4 - 1.5 mm
Quantity	30
Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PF
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3936 11T302