

Garant**CNMG indexable insert for roughing 50 pieces, HB7020-2, Size: 120408****Order data**

Order number	GG2417 120408
GTIN	4067263092582
Item class	GGN

Technical description

Cutting depth a_p	1.5 - 6 mm
Tool material	Carbide
Finishing/roughing assignment	Roughing
Cutting speed v_c main application	110 - 360 mm/min
Contents	250322 HB7020-2
Corner radius	0.8 mm
Main application	P
Number of changes/inserts	4
Cutting depth $a_{p \max}$	4.25 mm
Cutting depth $a_{p \min}$	0.55 mm
ISO code indexable insert	CNMG 120408

Data sheet

Feed f	0.25 - 0.6 mm/rev.
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2417 120408