

**VCGT indexable insert for medium machining 30 pieces, HU7310, Size: 110302****Order data**

Order number	GG3835 110302
GTIN	4067263098577
Item class	GGN

Technical description

Contents	261453 HU7310
ISO code indexable insert	VCGT 110302
Cutting depth a_p	0.1 - 4 mm
Main application	N
Cutting depth $a_{p \max}$	1.75 mm
Tool material	Carbide
Number of changes/inserts	2
Cutting speed v_c main application	350 - 600 mm/min
Feed f	0.05 - 0.5 mm/rev.
Coating	uncoated
Cutting depth $a_{p \min}$	0.15 mm
Tolerance	G
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing
Corner radius	0.2 mm
Quantity	30
Type	HU7310

Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3835 110302