


Value pack SNMG indexable insert roughing 30 pieces HB7020-2

Order data

Order number	GG2452 120408
GTIN	4067263093251
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.55 mm
Contents	251324 HB7020-2
Cutting speed v_c main application	110 - 360 mm/min
Feed f	0.25 - 0.6 mm/rev.
Corner radius	0.8 mm
Number of changes/inserts	8
Cutting depth a_p	1.5 - 6 mm
Finishing/roughing assignment	Roughing
Main application	P
ISO code indexable insert	SNMG 120408
Cutting depth $a_{p \max}$	4.25 mm

Tool material	Carbide
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2452 120408