

**VCMT indexable insert for medium machining 50 pieces, HBT130, Size: 160408****Order data**

Order number	GG2696 160408
GTIN	4067263097327
Item class	GGN

Technical description

Cutting depth a_p	0.3 - 2.5 mm
Cutting depth $a_{p \min}$	0.55 mm
Contents	261476 HBT130
ISO code indexable insert	VCMT 160408
Tool material	Carbide
Finishing/roughing assignment	Finishing
Main application	M
Cutting depth $a_{p \max}$	2.5 mm
Corner radius	0.8 mm
Coating	TiCN
Cutting speed v_c main application	50 - 200 mm/min
Number of changes/inserts	2
Quantity	50
Feed f	0.05 - 0.35 mm/rev.
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG2696 160408
