

Garant**FeedKing high feed rate milling cutter with bore, for indexable inserts XD..****Order data**

Order number	212910 32/5
GTIN	4045197549761
Item class	210

Description**Version:**

Dynamic cutting edge geometry for highest feed rates. Extremely smooth cutting due to **self-stabilising insert bedding**. **Optimised geometry** for reduced cutting forces, thereby reducing the stress on the main spindle.

Advantage:

Particularly cost-effective due to **exceptionally sturdy 4-edge** inserts.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size 9IP**.

Technical description

Overall length L_{tot}	40 mm
suitable indexable insert	XD.. 070308
Set of insert screws	219810 (9IP; 2.2 Nm)
$\varnothing D_3$	19 mm
Cutting edge $\varnothing D_c$	32 mm
maximum cutting depth $a_{p\max}$	0.85 mm
Mounting bore $\varnothing$	16 mm

Number of cutting edges Z	5
Through-coolant	yes
Circular interpolation milling $\varnothing D_{\min}$	51 mm
Circular interpolation milling $\varnothing D_{\max}$	62 mm
Circular interpolation milling a_p	0.85 mm
Ramping length L for $\alpha_{\max}$	18 mm
Ramping angle $\alpha_{\max}$	0.95 degrees
Series	FeedKing
Setting angle κ	10 degrees
Fz Helix	0.7
Shank type	with bore
Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Spacing of the cutters	unequal spacing
Machining strategy	HPC
Tool exchange	PowerCard
Type of product	Copy mill

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/212910-32/5>