

Garant**DCMT indexable insert for finishing 50 pieces, HB7130-2, Size: 11T304****Order data**

Order number	GG3517 11T304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.15 mm
Feed f	0.1 - 0.3 mm/rev.
Tolerance	M
Quantity	50
Cutting depth a_p	0.2 - 1.5 mm
Main application	M
Cutting depth $a_{p \max}$	2.75 mm
Number of changes/inserts	2
Tool material	Carbide
ISO code indexable insert	DCMT 11T302
Cutting speed v_c main application	80 - 270 mm/min

Data sheet

Finishing/roughing assignment	Finishing
Corner radius	0.2 mm
Contents	260359 HB7130-2
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3517 11T304