

Garant**Master Mute boring bar A.. SDUCR 93°, for indexable inserts DC., right****Order data**

Order number	265014 12/07
GTIN	4069515024624
Item class	29E

Description**Version:**

Round shank without clamping face. Carbide-reinforced shank.

Note:

Boring bar can be shortened as far as length L_{min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

ISO code toolholder	A12Q SDUCR/L07
Setting angle κ	93 degrees
Insert size	7 mm
Shank $\varnothing D_s$	12 mm
suitable indexable insert	DC.. 0702..
Standard	Works standard
Minimum pre-drill $\varnothing D_{min}$	16 mm
Overall length L	180 mm
Centre offset L_3	8.9 mm
Series	Master Mute
Set of insert screws	269028 38
Overhang L_1	132 mm
Application type	right-hand

Data sheet

Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar