

Garant**DCMT indexable insert for medium machining 30 pieces, HB7010-2, Size: 070204****Order data**

Order number	GG2819 070204
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	2
Tool material	Carbide
Main application	P
Cutting speed v_c main application	120 - 440 mm/min
Corner radius	0.4 mm
Cutting depth $a_{p \max}$	1.75 mm
Cutting depth a_p	0.3 - 2 mm
Feed f	0.08 - 0.3 mm/rev.
Finishing/roughing assignment	Finishing
Contents	260452 HB7010-2

Data sheet

ISO code indexable insert	DCMT 070204
Cutting depth $a_{p \min}$	0.25 mm
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2819 070204