

Garant**FeedKing high feed rate milling cutter with bore, for indexable inserts XD..****Order data**

Order number	212910 66/65
GTIN	4045197715302
Item class	210

Description**Version:**

Dynamic cutting edge geometry for highest feed rates. Extremely smooth cutting due to **self-stabilising insert bedding**. **Optimised geometry** for reduced cutting forces, thereby reducing the stress on the main spindle.

Advantage:

Particularly cost-effective due to **exceptionally sturdy 4-edge** inserts.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 5.7** with bit No. **674252 size 20IP**.

Technical description

Set of insert screws	219800 (20IP; 5.7 Nm)
$\varnothing D_3$	45 mm
maximum cutting depth $a_{p\max}$	1.8 mm
Overall length L_{tot}	50 mm
Cutting edge $\varnothing D_c$	66 mm

Mounting bore Ø	27 mm
suitable indexable insert	XD.. 120408
Number of cutting edges Z	6
Through-coolant	yes
Circular interpolation milling Ø D _{min}	111 mm
Circular interpolation milling Ø D _{max}	130 mm
Circular interpolation milling a _p	1.85 mm
Ramping length L for α _{max}	44.5 mm
Ramping angle α _{max}	0.39 degrees
Series	FeedKing
Setting angle κ	12 degrees
Fz Helix	0.7
Shank type	with bore
Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Spacing of the cutters	unequal spacing
Machining strategy	HPC
Tool exchange	PowerCard
Type of product	Copy mill

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/212910-66/6S>