

**Value pack cup brush steel wire 0,35 mm****Order data**

Order number	GG5730 60
GTIN	4067263136156
Item class	GGN

**Description****Version:**

Waved wire firmly crimped into the steel body. For use on angle grinders and on stationary machines.

With **M14 internal thread**.

Corresponds to No. 573005. With **M14 internal thread**.

**Application:**

Very well suited for brushing surfaces, deburring, removing rust, polishing, removing paint, primer, varnish, scale etc.

**Technical description**

maximum speed	12000 min <sup>-1</sup>
Length of brush section H <sub>1</sub>	20 mm
Brush Ø D <sub>1</sub>	65 mm
Bristle thickness	0.35 mm
Thread M	M14

Contents	5
Brush material	Steel wire
Type of product	Cup brush

### **Suitable products**

<https://www.hoffmann-group.com/GB/en/hom/p/GG5730-60>