

Garant**Value pack WNMG indexable insert medium machining 30 pieces HB7020-2****Order data**

Order number	GG2485 080412
GTIN	4067263093619
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	2 mm
Tool material	Carbide
Contents	252072 HB7020-2
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting depth a_p	0.3 - 4 mm
Number of changes/inserts	6
Corner radius	0.8 mm
Cutting speed v_c main application	130 - 370 mm/min
Main application	P

Data sheet

ISO code indexable insert	WNMG 080412
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2485 080412