

**DNMG indexable insert for medium machining 50 pieces, HBT130, Size: 150608****Order data**

Order number	GG3967 150608
GTIN	4067263094449
Item class	GGN

Technical description

Quantity	50
Feed f	0.15 - 0.55 mm/rev.
Cutting depth a_p	2 - 6 mm
Number of changes/inserts	4
Contents	250786 HBT130
Corner radius	0.8 mm
Tool material	Carbide
Coating	TiCN
Main application	M
Cutting speed v_c main application	40 - 180 mm/min

Data sheet

ISO code indexable insert	DNMG 150608
Cutting depth $a_{p \min}$	0.55 mm
Finishing/roughing assignment	Roughing
Cutting depth $a_{p \max}$	3.75 mm
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MR
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3967 150608