



VCMT indexable insert for medium machining 30 pieces, HBT130, Size: 160408

Order data

Order number	GG2695 160408
GTIN	4067263097310
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	2.5 mm
Main application	M
Contents	261476 HBT130
Corner radius	0.8 mm
Cutting depth $a_{p \min}$	0.55 mm
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
ISO code indexable insert	VCMT 160408
Cutting speed v_c main application	50 - 200 mm/min
Coating	TiCN
Tool material	Carbide
Cutting depth a_p	0.3 - 2.5 mm
Feed f	0.05 - 0.35 mm/rev.
Quantity	30
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG2695 160408
