

Garant**Value pack DNMG indexable insert roughing 30 pieces HB7010-2****Order data**

Order number	GG2431 150612
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.25 - 0.6 mm/rev.
Tool material	Carbide
Cutting depth $a_{p \max}$	3.75 mm
Cutting depth a_p	1.5 - 6 mm
Corner radius	1.2 mm
ISO code indexable insert	DNMG 150612
Number of changes/inserts	4
Cutting depth $a_{p \min}$	0.8 mm
Finishing/roughing assignment	Roughing
Main application	P
Contents	250864 HB7010-2

Data sheet

Cutting speed v_c main application	120 - 415 mm/min
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2431 150612