



Cordless drill / driver, Type: M12FDD2



Order data

Order number	070210 M12FDD2
GTIN	
Item class	03L

Description

Version:

MILWAUKEE – Cordless drill / driver Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display**. Sturdy **metal gearbox** for long working life. **FIXTEC metal quick-clamping drill chuck** with spindle lock. LED illumination of the working area. Handle with Softgrip coating for comfortable use.

- **Brushless POWERSTATE™ motor for more power and a compact shape (168 mm in length).**
- **REDLINK PLUS™ electronics for intelligent power management and overload protection.**
- **16-step electronic torque limit setting, plus drill steps.**

Advantage:

REDLINK PLUS™ electronics.

Supplied with:

Supplied with 2 pcs. 12 V / 2.0 Ah Li-ion batteries, charger, belt clip, HD box.

Technical description

Weight	1.2 kg
--------	--------

maximum twist drill size Ø in steel	13 mm
maximum twist drill size Ø in wood	35 mm
maximum vibration to EN	< 2.5 m/s ²
typical application	Strong
Battery capacity	2 Ah
Quick-clamping chuck range	1.5 - 13 mm
maximum speed 2nd speed	1700 min ⁻¹
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
maximum speed 1st speed	0 - 450 min ⁻¹
maximum torque hard	37 Nm
Packaging	Modular case (HD=Heavy Duty)
Manufacturer's designation	M12FDD-202X
Motor design	Brushless motor
Battery voltage	12 V
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Steel
Suitable for material	Metal
Type of product	Drill/driver

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/070210-M12FDD2>