




Safety coupling Hose connection, Hose connection internal Ø (nominal bore): 11mm



Order data

Order number	080278 11
GTIN	7391390419033
Item class	08A

Description

Version:

Steel couplings have many advantages in pneumatic systems compared to standard brass couplings:

- **Easy to use with only one hand with low coupling force.**
- **High flow rate as a consequence of very low pressure drop.**
- **Long working life due to surface treatment and hardened components with tight manufacturing tolerances.**
- **Cost-effectiveness - the amortisation time is 2 years at the most.**

The **eSafe safety coupling** satisfies the ISO standard 4414 and EN 983 It is first depressurised and then decoupled in a second step (no whiplash). New improved single-handed operation. Rate of flow: 950 ltr/min, maximum operating pressure 16 bar. Complies with ISO standard B.

Application:

For improving the performance, economics, and safety of industrial compressed air installations.

Note:

The CEJN series 310 is suitable for the markets of Benelux, France, North America and Norway.

Technical description

Hose connection internal Ø (nominal bore)	11 mm
Flow rate	950 l/min
maximum operating pressure	16 bar

Material	Steel coupling
Type of product	Coupling