

**SCMT indexable insert for medium machining 50 pieces, HB7010-2, Size: 120408****Order data**

Order number	GG2836 120408
GTIN	4067263092278
Item class	GGN

Technical description

Tool material	Carbide
Cutting speed v_c main application	120 - 440 mm/min
Main application	P
Number of changes/inserts	4
Contents	260766 HB7010-2
Corner radius	0.8 mm
Cutting depth $a_{p \max}$	4.25 mm
ISO code indexable insert	SCMT 120408
Quantity	50
Feed f	0.08 - 0.3 mm/rev.

Data sheet

Finishing/roughing assignment	Finishing
Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \min}$	0.55 mm
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2836 120408