

**Value pack flow drill - standard (with collar) long Inox, 5 pieces****Order data**

Order number	GG0756 M10
GTIN	4069515043014
Item class	GGN

Description**Version:**

Very quickly produce core holes in thin-walled materials using frictional heat. Can be used on CNC, NC and pillar drilling machines.

Flow drill - standard (with collar), for use in stainless materials, **same as No. 080756.**

Standard or long; with or without a collar.

Application:

Particularly suitable for stainless steels.

Suitable for:

HOLEX ER collets No. 308964, ER chuck key No. 309680, HOLEX fluteless tap No. 139130 or No. 139180 and HOLEX holder M-Drill No. 080750.

Technical description

recommended speed	2100 min ⁻¹
recommended drive power	1.7 kW
Material thickness	0.7 - 3 mm
Shank Ø	10 mm

Data sheet

Tapping hole Ø	9.3 mm
Contents	5" pcs.
Type of product	Flow drills

Suitable products

No Shop URL available for: GG0756 M10