

**CNMG indexable insert for medium machining 30 pieces, HB7140-2, Size: 160612****Order data**

Order number	GG2908 160612
GTIN	4067263092278
Item class	GGN

Technical description

Tool material	Carbide
Finishing/roughing assignment	Finishing
Corner radius	1.2 mm
Number of changes/inserts	4
Contents	250170 HB7140-2
ISO code indexable insert	CNMG 160612
Cutting depth $a_{p \max}$	5.5 mm
Tolerance	M
Cutting depth a_p	0.5 - 4 mm
Main application	M

Data sheet

Feed f	0.1 - 0.4 mm/rev.
Quantity	30
Cutting depth $a_{p \min}$	0.8 mm
Cutting speed v_c main application	60 - 200 mm/min
Coating	coated
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2908 160612