



Safety cabinet Q-Pegasus type 90, Width: 600mm



Order data

Order number	981015 600
GTIN	2050001709790
Item class	96G

Description

Version:

Cabinet casing of sheet metal with integral door position detector, interior with chemically resistant surface.

- **Mountings for shelves at 32 mm intervals.**
- **Floor-level containment tray (satisfies StawaR).**
- **With exhaust air connection (NB 75).**
- **Including door position detector.**
- **Lockable with profile half-cylinder, can be integrated into the company's locking system. Not compatible with the Hoffmann locking system.**
- **With 4 height adjustment feet to compensate for unevenness in the floor.**

With **AGT** (Asynchronously Linked Door Drive), **TSA** (Automatic Door Closer) with visual and acoustic warning of automatic door closing. 1-door

Application:

Secure storage in accordance with regulations of flammable hazardous substances in work areas.

Standard:

DIN EN 14470-1, type tested (fire chamber tested), **90 minutes fire resistant (satisfies the highest fire protection class of the TRGS 510 Appendix 1).**

Supplied with:

Cabinet with 3 storage shelves, perforated panel insert and floor-level drip tray, plastic-coated and base fascia, 1 service log book.

Colour:

Cabinet casing RAL 7016 anthracite grey, doors **signal blue RAL 5005**.

Note:

At regular intervals (annually), safety cabinets should be maintained and their operating characteristics checked by an authorised competent person.

Technical description

Usable width	450 mm
Usable height	1647 mm
Number of floor-level containment trays	1
Number of shelves	3
Width	599 mm
Number of perforated plate inserts	1
Volume of floor-level drip tray	22 l
Depth	615 mm
Usable depth	522 mm
Height	1953 mm
Load capacity of shelf	75 kg
Weight	315 kg
Height adjustment interval	32 mm
Colour selection	Body RAL 7016, fronts RAL 7035, 1004, 3020, 5010, 5005, 6011, 9010, 9006
Fire resistance	90 min
Type of product	Safety cabinet