

Garant**CNMG indexable insert for medium machining 50 pieces, HB7010-2, Size: 160612****Order data**

Order number	GG2410 160612
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	5.5 mm
Main application	P
Feed f	0.2 - 0.5 mm/rev.
Corner radius	1.2 mm
Cutting depth $a_{p \min}$	0.8 mm
Cutting speed v_c main application	140 - 440 mm/min
Number of changes/inserts	4
Finishing/roughing assignment	Finishing
Contents	250170 HB7010-2
Cutting depth a_p	0.3 - 4 mm

Tool material	Carbide
ISO code indexable insert	CNMG 160612
Quantity	50
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2410 160612