

**DCMT indexable insert for medium machining 30 pieces, Size: 070204****Order data**

Order number	GG2666 070204
GTIN	4067263096535
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.05 - 0.35 mm/rev.
Tool material	Carbide
Main application	M
Finishing/roughing assignment	Finishing
Coating	TiCN
Number of changes/inserts	2
Contents	260500 HBT130
Cutting depth a_p	0.3 - 2.5 mm
ISO code indexable insert	DCMT 070204
Cutting speed v_c main application	50 - 200 mm/min
Cutting depth $a_{p \max}$	1.75 mm
Corner radius	0.4 mm
Quantity	30
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2666 070204

