



CNMG indexable insert for medium machining 50 pieces, HBT020, Size: 160608



Order data

Order number	GG3903 160608
GTIN	4067263092568
Item class	GGN

Technical description

Coating	TiCN
Number of changes/inserts	4
Cutting depth a_p	0.8 - 5 mm
Finishing/roughing assignment	Finishing
Contents	250204 HBT020
Corner radius	0.8 mm
Cutting speed v_c main application	100 - 280 mm/min
Cutting depth $a_{p \max}$	5.5 mm
Feed f	0.1 - 0.45 mm/rev.
Tool material	Carbide
Main application	P
Cutting depth $a_{p \min}$	0.55 mm
ISO code indexable insert	CNMG 160608

Data sheet

Quantity	50
Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3903 160608