



## Value pack cup brush steel wire 0,35 mm



### Order data

Order number	GG5730 100
GTIN	4067263136170
Item class	GGN

### Description

**Version:**

Waved wire firmly crimped into the steel body. For use on angle grinders and on stationary machines.

**With M14 internal thread.**

Corresponds to No. 573005. With **M14 internal thread**.

**Application:**

Very well suited for brushing surfaces, deburring, removing rust, polishing, removing paint, primer, varnish, scale etc.

### Technical description

Thread M	M14
maximum speed	8500 min <sup>-1</sup>
Brush Ø D <sub>1</sub>	100 mm
Bristle thickness	0.35 mm
Length of brush section H <sub>1</sub>	30 mm

Contents	5
Brush material	Steel wire
Type of product	Cup brush

## **Suitable products**

<https://www.hoffmann-group.com/GB/en/hom/p/GG5730-100>