

**VCMT indexable insert for medium machining 30 pieces, HB7120-1, Size: 160408****Order data**

Order number	GG3570 160408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	80 - 260 mm/min
Feed f	0.1 - 0.4 mm/rev.
Main application	M
Cutting depth $a_{p \max}$	2.5 mm
ISO code indexable insert	VCMT 160408
Cutting depth a_p	0.5 - 2.5 mm
Contents	261459 HB7120-1
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.55 mm
Tolerance	M
Number of changes/inserts	2
Corner radius	0.8 mm
Tool material	Carbide
Quantity	30
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG3570 160408
