

**TCMT indexable insert for medium machining 50 pieces, HB7010-2, Size: 16T308****Order data**

Order number	GG2848 16T308
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.08 - 0.3 mm/rev.
Corner radius	0.8 mm
Cutting depth $a_{p \min}$	0.55 mm
Quantity	50
Number of changes/inserts	3
ISO code indexable insert	TCMT 16T308
Main application	P
Cutting speed v_c main application	120 - 440 mm/min
Cutting depth a_p	0.3 - 2 mm
Contents	260988 HB7010-2

Data sheet

Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	4 mm
Tool material	Carbide
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2848 16T308