

**SNMG indexable insert for medium machining 50 pieces, HB7120-1, Size: 120408****Order data**

Order number	GG2947 120408
GTIN	4067263092278
Item class	GGN

Technical description

Tool material	Carbide
Cutting speed v_c main application	80 - 260 mm/min
Contents	251224 HB7120-1
Feed f	0.1 - 0.4 mm/rev.
Cutting depth a_p	0.5 - 4 mm
Corner radius	0.8 mm
Quantity	50
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.55 mm
Cutting depth $a_{p \max}$	4.25 mm
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8
Main application	M
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2947 120408
