

Garant**SCGT indexable insert for medium machining 50 pieces, HB7310, Size: 09T304****Order data**

Order number	GG3824 09T304
GTIN	4067263098263
Item class	GGN

Technical description

Cutting depth a_p	0.1 - 4 mm
Corner radius	0.4 mm
Quantity	50
Feed f	0.05 - 0.5 mm/rev.
Cutting depth $a_{p \min}$	0.25 mm
Cutting speed v_c main application	350 - 600 mm/min
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	3.25 mm
Tool material	Carbide
Number of changes/inserts	4
ISO code indexable insert	SCGT 09T304

Main application	N
Contents	260762 HB7310
Tolerance	G
Type	HB7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3824 09T304