

**CCMT indexable insert for medium machining 30 pieces, HB7020-2, Size: 120408****Order data**

Order number	GG2808 120408
GTIN	4067263095255
Item class	GGN

Technical description

Feed f	0.08 - 0.3 mm/rev.
Corner radius	0.8 mm
Number of changes/inserts	2
Cutting depth $a_{p \max}$	4.25 mm
Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \min}$	0.55 mm
Main application	P
Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting speed v_c main application	110 - 350 mm/min

Data sheet

Contents	260160 HB7020-2
ISO code indexable insert	CCMT 120408
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2808 120408