

**CNMG indexable insert for medium machining 50 pieces, HB7120-1, Size: 160608****Order data**

Order number	GG2909 160608
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	CNMG 160608
Cutting depth $a_{p \min}$	0.55 mm
Number of changes/inserts	4
Cutting depth a_p	0.5 - 4 mm
Contents	250168 HB7120-1
Tolerance	M
Tool material	Carbide
Corner radius	0.8 mm
Main application	M
Cutting speed v_c main application	80 - 260 mm/min
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	5.5 mm
Quantity	50
Feed f	0.1 - 0.4 mm/rev.
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG2909 160608
