

Garant**SNMG indexable insert for medium machining 50 pieces, HB7140-2, Size: 120404****Order data**

Order number	GG2949 120404
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	8
Coating	coated
Contents	251222 HB7140-2
Main application	M
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.5 - 4 mm
Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.1 - 0.4 mm/rev.
Tool material	Carbide
Cutting depth $a_{p \max}$	4:25 mm

Data sheet

Corner radius	0.4 mm
Quantity	50
ISO code indexable insert	SNMG 120404
Cutting speed v_c main application	60 - 200 mm/min
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2949 120404