

**CNMG indexable insert for medium machining 30 pieces, HB7140-2, Size: 120416****Order data**

Order number	GG2908 120416
GTIN	4067263092278
Item class	GGN

Technical description

Coating	coated
Main application	M
Feed f	0.1 - 0.4 mm/rev.
ISO code indexable insert	CNMG 120416
Contents	250162 HB7140-2
Tool material	Carbide
Cutting depth $a_{p \max}$	4:25 mm
Number of changes/inserts	4
Cutting depth a_p	0.5 - 4 mm
Quantity	30

Data sheet

Corner radius	1.6 mm
Cutting depth $a_{p \min}$	1.05 mm
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	60 - 200 mm/min
Tolerance	M
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2908 120416