

Garant**DCMT indexable insert for finishing 50 pieces, HB7020-2, Size: 070202****Order data**

Order number	GG2817 070202
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.15 mm
Contents	260351 HB7020-2
ISO code indexable insert	DCMT 070202
Corner radius	0.2 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting depth a_p	0.2 - 1.5 mm
Main application	P
Cutting speed v_c main application	140 - 400 mm/min
Feed f	0.07 - 0.25 mm/rev.
Number of changes/inserts	2

Data sheet

Cutting depth $a_{p \max}$	1.75 mm
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2817 070202