

**VCMT indexable insert for finishing 30 pieces, HBT130, Size: 110304****Order data**

Order number	GG2693 110304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	60 - 220 mm/min
Cutting depth a_p	0.1 - 1 mm
Cutting depth $a_{p \max}$	1.75 mm
ISO code indexable insert	VCMT 110304
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
Tool material	Carbide
Feed f	0.05 - 0.2 mm/rev.
Corner radius	0.4 mm
Coating	TiCN
Cutting depth $a_{p \min}$	0.25 mm
Main application	M
Contents	261386 HBT130
Quantity	30
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MF
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2693 110304
