

**CNMG indexable insert for finishing 50 pieces, HB7010-2, Size: 120408****Order data**

Order number	GG2403 120408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.3 - 2 mm
Cutting speed v_c main application	170 - 500 mm/min
Number of changes/inserts	4
Feed f	0.1 - 0.4 mm/rev.
Contents	250060 HB7010-2
Cutting depth $a_{p \min}$	0.55 mm
Main application	P
Finishing/roughing assignment	Finishing
Tool material	Carbide
Corner radius	0.8 mm
Cutting depth $a_{p \max}$	4.25 mm

ISO code indexable insert	CNMG 120408
Quantity	50
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2403 120408