

Computer workstation with printer flap, mobile, Type: DE



Order data

Order number	948262 DE
GTIN	4062406074579
Item class	9GS

Description

Version:

Computer cabinet with separately lockable double-leaf door with polycarbonate window or with printer flap. Fitted with partition for the tower compartment with galvanised storage shelf, pull-out shelf (load capacity 45 kg) with strain relief. Keyboard drawer with recessed and removable storage tray, palm rest made from bamboo and strain relief. Locking with a common key. Cable pass-through on the rear of the housing. Storage shelf made of bamboo.

With mobile base composed of 2 fixed wheels and 2 electrically conductive castors with brakes Ø 125 mm and push handles.

With space-saving TFT monitor housing for flat screens, lockable, with storage compartment for cables. Self-supporting steplessly adjustable lift door with polycarbonate window.

Supplied with:

The fixed **electrical installation** includes multi-way socket (6-way, 250 V / 16 A with ON / OFF switch), 1.2 m connecting cable and a fan for protection against overheating.

Colour:

Body and keyboard drawer RAL 7035 light grey, doors, drawer front and pull-out shelf RAL 7016 anthracite **powder-coated**.

Technical description

Data sheet

Depth in G	28
Monitor housing usable height	460 mm
Dimensions printer flap	346×290 mm
Monitor housing usable depth	230 mm
Monitor housing usable width	690 mm
Depth	700 mm
Height	1770 mm
Width in G	40
Weight	120 kg
Width	1000 mm
Support cabinet usable width left	700 mm
Support cabinet usable width right	223 mm
Support cabinet usable height	645 mm
On/Off switch	yes
Nominal voltage	250 V
#Plug type, input	F
Wheel Ø	125 mm
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Computer workstation

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/948262-DE>