Data sheet

Garant

DCGT indexable insert for finishing 50 pieces, HU7315-1, Size: 11T304

Order data

Order number	GG3812 11T304
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Number of changes/inserts	2
ISO code indexable insert	DCGT 11T304
Feed f	0.03 - 0.1 mm/rev.
Cutting depth $a_{p\,min}$	0.05 mm
Cutting depth a_p	0.05 - 0.6 mm
Contents	260359 HU7315-1
Tool material	Carbide
Cutting speed v_c main application	120 - 600 mm/min
Coating	uncoated
Quantity	50
Cutting depth $a_{p\,max}$	0.2 mm
Main application	N
Corner radius	0.4 mm
Tolerance	G
Type	HU7315-1
Cutting conditions	continuous
Chip breaker	AF

Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3812 11T304