

**SNMG indexable insert for medium machining 30 pieces, HB7130-2, Size: 120404****Order data**

Order number	GG2945 120404
GTIN	4067263094630
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.55 mm
ISO code indexable insert	SNMG 120404
Cutting speed v_c main application	70 - 240 mm/min
Feed f	0.1 - 0.4 mm/rev.
Cutting depth $a_{p \max}$	4:25 mm
Coating	coated
Contents	251222 HB7130-2
Main application	M
Corner radius	0.4 mm
Cutting depth a_p	0.5 - 4 mm
Tool material	Carbide
Quantity	30
Number of changes/inserts	8
Finishing/roughing assignment	Finishing
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG2945 120404
