

**DCMT indexable insert for medium machining 50 pieces, HB7140-2, Size: 11T304****Order data**

Order number	GG3525 11T304
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	DCMT 11T304
Main application	M
Tolerance	M
Quantity	50
Cutting depth a_p	0.5 - 2.5 mm
Number of changes/inserts	2
Feed f	0.1 - 0.4 mm/rev.
Coating	coated
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	2.75 mm
Corner radius	0.4 mm
Contents	260462 HB7140-2
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	60 - 200 mm/min
Tool material	Carbide
Type	HB7140-2
Cutting conditions	heavily interrupted

Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3525 11T304