

Garant

Short drill chuck Form AD, BT 40, Clamping range: 0,5-13mm



Order data

Order number	303171 0,5-13
GTIN	4045197937957
Item class	31B

Description

Version:

For clockwise and anticlockwise rotation.

Concentricity $\leq 20 \mu\text{m}$.

- **Slim design.**
- **Specific coolant transfer to tools with IC.**
- **Optimum holding torques at the tool.**

With through coolant feed up to max. 50 bar.

Supplied with:

Clamping wrench.

Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

External $\varnothing$ D	43 mm
Overhang dimension A	92 mm
Clamping range	0.5 - 13 mm

Spare Torx® chuck key No. 625220	TX25
Adapter	BT 40
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	AD
Through-coolant	yes, with max. 50 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 20 µm
maximum tightening torque $M_{d\ max}$	≤ 14 Nm
Type of product	Short drill chuck

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/303171-0,5-13>