


Master Mute boring bar A.. SDUCL 93°, for indexable inserts DC.., left

Order data

Order number	265015 16/07
GTIN	4069515024754
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Boring bar can be shortened as far as length L_{min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Shank $\varnothing D_s$	16 mm
Overall length L	158 mm
Overhang L_1	96 mm
Series	Master Mute
Insert size	7 mm
Centre offset L_3	11 mm
Standard	Works standard
Setting angle κ	93 degrees
ISO code toolholder	A16X SDUCR/L07
suitable indexable insert	DC.. 0702..
Set of insert screws	269028 38
Minimum pre-drill $\varnothing D_{min}$	20 mm
L_{min}	96 mm

Data sheet

Application type	left-hand
Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar