

Garant**CNMG indexable insert for medium machining 50 pieces, HB7010-2, Size: 09T308****Order data**

Order number	GG2410 09T308
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Cutting speed v_c main application	140 - 440 mm/min
ISO code indexable insert	CNMG 09T308
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	4
Main application	P
Cutting depth $a_{p \text{ min}}$	0.55 mm
Contents	250152 HB7010-2
Cutting depth $a_{p \text{ max}}$	3.25 mm
Tool material	Carbide

Data sheet

Cutting depth a_p	0.3 - 4 mm
Corner radius	0.8 mm
Quantity	50
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2410 09T308