


Garant**Value pack GARANT Master Steel solid carbide mini milling cutter HPC, 5 pieces****Order data**

Order number	GG2295 1,2
GTIN	4067263091400
Item class	GGN

Description**Version:**

Extra short cutter for maximum stability. **Shank length to DIN** for improved support of the tool in the holder. This significantly increases the tool life.

Save the regrinding costs: It is cheaper to use a carbide mini milling cutter to the limit of wear and throw it away, than to regrind it.

Same as No. 202295.

Technical description

Feed f_z for slot milling in steel $< 900 \text{ N/mm}^2$	0.005 mm
No. of teeth Z	3
Corner chamfer width at 45°	0.02 mm
Shank	DIN 6535 HA to h6
Overall length L	38 mm
Tolerance nominal $\varnothing$	e8

Cutting edge $\varnothing D_c$	1.2 mm
Shank $\varnothing D_s$	3 mm
Direction of infeed	horizontal, oblique and vertical
Helix angle	45 degrees
Shank form	HA
Flute length L_c	2 mm
Corner chamfer angle	45 degrees
Contents	5
Feed f_z for side milling in steel < 900 N/mm ²	0.006 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Works standard
Type	N
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	0.5×D for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	290 m/min	N
Alu > 10% Si	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm ²	suitable	140 m/min	P
Steel < 750 N/mm ²	suitable	120 m/min	P

Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable	50 m/min	P
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	70 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	40 m/min	S
GG(G)	suitable	85 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Accessories

GARANT Master Steel solid carbide mini milling cutterHPC
Ø e8 DC 1,2 mm

202295 1,2