

Garant**Solid carbide drill plain shank DIN 6535 HA 180°, TiAlN, Ø DC m7: 10,01-Xmm**

Order data

Order number	122506 10,01-X
GTIN	4062406200824
Item class	11E

Description

Version:

Special point geometry for generating **180° flat-bottomed holes**. Low radial forces even when spot drilling on faces with up to 45° slope. Flute geometry for optimum chip evacuation. With 4 guide chamfers to stabilise the drill in the hole.

Advantage:

The 180° point angle permits drilling and counterboring in a single operation.

Recommendation:

When using the solid carbide 180° drill it is absolutely essential for process reliability:

- **when spot drilling on flat surfaces to drill a pilot hole 1xD using pilot drill No. 122736.**
- **when spot drilling on sloping surfaces up to 15° : reduce the feed rate f to 50 %, up to 30°: reduce the feed rate f to 40 % and up to 45°: reduce the feed rate f to 25 % of the stated value. After spot drilling, the normal feed rate value can be used.**

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122506 + 129100HB**.

Form **HE**: order with **No. 122506 + 129100HE**.

180° solid carbide drills for machining aluminium available on request.

Not suitable for generating counterbores for socket-head screws to DIN974-1. Delivery time: 8 weeks

Minimum order quantity: 3 pcs.

Items made to order for a specific customer: Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement. Items cannot be returned. We reserve the right to over-deliver or under-deliver by +/-10% (minimum 1 piece).

Technical description

Data sheet

Standard	Manufacturer's standard
Number of cutting edges Z	2
Overall length L	100 mm
Tolerance nominal Ø	h7
Flute length L _c	53 mm
Shank Ø D _s	12 mm
Ø range	10.01 - 12 mm
Coating	TiAlN
Tool material	Solid carbide
Version	3×D
Point angle	180 degrees
Shank	DIN 6535 HA to h6
Use for drilling	limited convexity
Use for drilling	limited cross-drilling
Use for drilling	limited oblique spot drilling
Through-coolant	yes, with 25 bar
Pilot drill required	yes, pilot drill
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	85 m/min	P
Steel < 750 N/mm ²	suitable	75 m/min	P
Steel < 900 N/mm ²	suitable	60 m/min	P
Steel < 1100 N/mm ²	suitable	50 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	45 m/min	M

Data sheet

GG(G)	suitable	90 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
Air	suitable		