

Garant**DCGT indexable insert for medium machining 50 pieces, HB7310, Size: 11T302****Order data**

Order number	GG3818 11T302
GTIN	4067263098102
Item class	GGN

Technical description

Main application	N
Corner radius	0.2 mm
Feed f	0.05 - 0.5 mm/rev.
Cutting speed v_c main application	350 - 600 mm/min
Number of changes/inserts	2
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting depth $a_{p \max}$	2.75 mm
Quantity	50

Data sheet

Cutting depth a_p	0.1 - 4 mm
ISO code indexable insert	DCGT 11T302
Cutting depth $a_{p \min}$	0.15 mm
Contents	260458 HB7310
Tolerance	G
Type	HB7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3818 11T302