



Value pack flow drill - standard (with collar) Inox, 5 pieces



Order data

Order number	GG0752 M8
GTIN	4069515042789
Item class	GGN

Description

Version:

Standard or long; with or without a collar.

Very quickly produce core holes in thin-walled materials using frictional heat. Can be used on CNC, NC and pillar drilling machines.

Flow drill - standard (with collar), for use in stainless materials, **same as No. 080752**.

Application:

Particularly suitable for stainless steels.

Suitable for:

HOLEX ER collets No. 308964, ER chuck key No. 309680, HOLEX fluteless tap No. 139130 or No. 139180 and HOLEX holder M-Drill No. 080750.

Technical description

recommended speed	2300 min ⁻¹
Material thickness	0.7 - 1 mm
Tapping hole Ø	7.4 mm
recommended drive power	1.5 kW

Shank Ø	8 mm
Contents	5" pcs.
Type of product	Flow drills

Suitable products

No Shop URL available for: GG0752 M8