

Garant
Value pack CNMG indexable insert medium machining 30 pieces HB7035-2

Order data

Order number	GG2409 160608
GTIN	4067263092278
Item class	GGN

Technical description

Contents	250168 HB7035-2
Corner radius	0.8 mm
Cutting depth $a_{p \max}$	5.5 mm
ISO code indexable insert	CNMG 160608
Tool material	Carbide
Main application	P
Cutting depth a_p	0.3 - 4 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting depth $a_{p \min}$	0.55 mm
Cutting speed v_c main application	120 - 320 mm/min
Number of changes/inserts	4

Data sheet

Finishing/roughing assignment	Finishing
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2409 160608